



Replacement salt bridge for pH sensor, outer-junction, PPS Salt Bridge, PVDF

Nr. produs:

SB-R1SV

Produse periculoase

RON Preț (fără TVA):
Disponibil

Contact



Lowers Lifetime Cost of Process pH Sensors

The double junction salt bridge on all Hach pHDTM Differential pH / ORP Sensors is field-replaceable, and includes a FKM/FPM O-ring. Salt bridges are shipped in a salt solution to prevent dehydration / dry-out and can be stored in the shipping solution until needed. Salt bridges are available in a variety of materials and pre-packaged quantities.

Specificații

Material:	PPS
Note speciale:	Each salt bridge has a ceramic inner junction, FKM/FPM O-ring, and contains binary, equi-transferrant fill solution. (Salt bridges are shipped in a salt solution.)