



Be Right™



## High Output Airblast, 230V

Nr. produs: 6860103.99.0001

**ARTICOL ÎNVECHIT**  
Acest articol nu mai este disponibil.

Produce înlocuitoare sugerate:

- 6860100.99.0002

Automatic cleaning system for AN-ISE sc, AISE sc, NISE sc and LDO sc

### Specificații

Adancime:	compressor
Carcasă impermeabilă (IP) :	IP66 / NEMA 4X
Cerin#e de alimentare (Hz):	50 Hz
Cerin#e de alimentare (Tensiune):	230 V AC
Condi#ii de depozitare:	-20 °C to 70 °C ; 95% Relative Humidity
Condi#ii de operare:	-20 - 50 °C at 0 - 95% RH (non-condensing)
Debit:	1 m <sup>3</sup> /h output Air Flow Rate at compressor outlet
Dimensiuni (Înălțime x Lățime x Adâncime):	370 mm x 320 mm x 200 mm
Frecventa de lucru:	60 s for every 15 minutes
Greutate:	10.7 kg compressor
Inaltime:	compressor
Interval de presiune:	2.76 bar output air pressure at compressor outlet
IP siguranta:	250 V 5 A, controller relay
Latime:	compressor
Principiu de masurare:	High output air blast system for attachment to select sensors to reduce biogrowth and other types of fouling