



Hach AE Grade Filters, 125 mm, 100/pk

Nr. produs: 2551462

RON Preț (fără TVA): Contact

Nu este afișată data expirării

Filters feature fast flow rates, fine porosity and particle retention of 1.0µm which make them ideal for many dissolved and suspended solids testing procedures.

Filters feature fast flow rates, fine porosity and particle retention of 1.0µm which make them ideal for many dissolved and suspended solids testing procedures.

Hach Grade AE filters are comparable to Pall Type A/E filters and the 47mm diameter is compatible with the magnetic filter holder #1352900. Filters feature fast flow rates, fine porosity and particle retention of 1.0µm which make them ideal for many dissolved and suspended solids testing procedures including Standard Methods 2540 C, 2540 D and 2540 E. This binder-free, borosilicate glass microfiber filter has a DOP efficiency of 99.98% (0.3µm) and a maximum operating temperature of 550°C in air.

Specificații

Cantitate:	100 /pk
Diametru:	125 mm
Dimensiune por:	1.0 µm
Material:	Glass Microfiber