



## Acidification/Cleaning Unit for Amperometric Sensors

**Nr. produs:** LZY051  
**RON Preț (fără TVA):** Contact  
**Expediere în 2 săptămâni**

Many amperometric processes have optimal pH ranges in which they will be most accurate and produce the best results. Adding an acidification/cleaning unit onto instruments such as the CL10 sc can help to ensure that samples stay range that is favorable for measurement.

---

### Specificații

Cerin#e de alimentare (Tensiune):	12 V DC
Conținutul cutiei:	Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.
Debit:	Min 0.24, max. 1 mL/min
Depth panel:	107 mm
Garanție:	24 luni
Height (panel):	270 mm
IP siguranta:	T, 250 mA, 250V
Lungime cablu:	1 m digital
Material:	Carboy: PEHD (high-density polyethylene)
Toleran#ă produs:	0.125 " NPT (for tube fittings)
Volum:	10 L chemicals not supplied
Width:	250 mm

---

### Conținutul cutiei

Acidification Unit, Carboy, 1 M digital extension cable, Tubing Kit, and Instructions.