



Digital extension cable for SC sensors, 30 m

Nr. produs: **LZX852**
RON Preț (fără TVA): Contact
Nu este afișată data expedierii

Specificații

Cod cabluri:	AWG 22: brown (+12 V DC) Black (circuit common) AWG 26: white (data -) blue (data +)
Condiții de operare:	- 80 °C Fixed Installation
Diametru exterior :	6.8 mm ± 0.3 mm
Lungime cablu:	30 m
Material:	Cable: Cu: AWG 22 - 19×0.15 mm AWG 26 - 18×0.10 mm
Minimal bend radius:	7.5 × outer diameter, flexible installation
Minimal bend radius 2:	5 × outer diameter, fixed installation
Outside coat:	PUR (Elastoplan 1185), RoHS-conformal
Rezistența cabluri:	max. 260 Ω/km AWG 26 at 20 °C (loop)
Rezistența flux:	ca. 95 Ω at 1 kHz, AWG 22 pairs
Rezistența izolație:	≥ 20 MΩ × km at 20 °C
Shield attenuation:	≥ 55 dB
Tensiune de măsurare:	1200 V Vrms
	wire/wire
Total armatura:	Cu- netting, tinned

Voltaj normal:

250 V Vpp