



Polymetron 8398.5 Inductive conductivity sensor, 1" thread

Nr. produs: 08398=A=5000

RON Preț (fără TVA): Contact

Expediere în 2 săptămâni

Immersion probe for conductivity measurements also under harsh conditions. Polyetheretherketone (PEEK) body, 5m cable, runs with several types of controllers. In-built temperature element.

High chemical and mechanical resistance

Accuracy over a wide measuring range

For some types: perfect compact sanitary design for 2"/DN50 access port in compliance with 3A standards

Maintenance free: No electrode damage, no polarisation effect

Versatile mounting options: flow-through adapters and chambers, immersion shafts

Specificații

Cablu senzor:	1" outer thread for immersion applications
Condiții de operare:	140 °C maximum
Constanta celulei, k:	2.35
Domeniu de măsurare:	0,2 - 2000 mS/cm
Greutate:	0,700 kg
Interval de presiune:	Max. 18 bar
Lungime cablu:	5 m fixed cable
Material:	Gasket: EPDM; PEEK
Materiale în contact cu mediul:	PEEK
Principiu de măsurare:	Inductive conductivity measurement
Repetabilitate:	< ± 2 % sau ± 0.004 mS/cm, saucare este mai mare

Accesorii necesare

- Controller SC4500, Prognosys, ieșire 5x mA, 2 senzori digitali, 100-240 V c.a., fără cablu de alimentare (Item LXV525.99A11551)
- Controller SC4500, activat cu Claros, ieșire 5x mA, 2 senzori digitali, 100-240 V c.a., fără cablu de alimentare (Item LXV525.99AA1551)
- Controller SC4500, activat cu Claros, ieșire 5x mA, 2 senzori digitali, 100-240 V c.a., mufă UE (Item LXV525.99CA1551)
- SC4500 Controller, Prognosys, 5 x ieșire mA, un senzor digital, 100-240 V c.a., fără cablu de alimentare (Item LXV525.99A11501)

- SC4500 Controler, Prognosys, 5 x ie#ire mA, doi senzori digitali, 24 V c.c., fără mufă (Item LXV525.99Z11551)