



Filters, Hach 934-AH, 47 mm, 100/pk

Nr. produs: 2511207

RON Preț (fără TVA): Contact

Disponibil

Hach 934-AH Filters are specified for use in Standard Methods 2540 C, 2540 D and 2540 E. Fast flow rate, fine porosity and 1.5 μ m particle retention have made this binderless borosilicate glass microfiber filter the accepted industry standard for over 50 years. Hach 934-AH Filters can withstand temperatures over 500°C which is a unique and especially important feature for laboratories performing Fixed and Volatile Solids analysis of water and wastewater.

934-AH is a registered trademark of Whatman, Inc./GE Healthcare and used under license.

Specificații

Cantitate:	100 /pk
Diametru:	47 mm
Dimensiune por:	1.5 μ m
Material:	Glass Microfiber
Unitate:	100/pk