



EZ9010 Filtration System, for immersion, pore size 50 µm, 3 m tubing

Nr. produs:

EZ9010.XX310A01

ARTICOL ÎNVECHIT

Acest articol nu mai este disponibil.

Universal self-cleaning filtration systems - compatible with all EZ Series online analysers

About the EZ9000 Series

The successful implementation of online analysers in process control strategies could not have been achieved without the development of a new generation of automatic sampling and sample preconditioning systems. The EZ9000 Series are the result of many years of field experience in combining analysers with filtration units.

Simplified operation by self-cleaning action

All preconditioning systems are designed for fully automatic operation and require virtually no human intervention. Basically all systems are incorporated either with a blowback action by instrument air, or a specific cleaning cycle. This fundamental design principle does not merely allow trouble-free sampling, moreover it contributes to high uptimes.

The EZ9010 systems are front runners of the filtration series and the standard designed for reliably delivering filtered samples to an online analyser. The self-cleaning feature of the unit includes a blowback action with sample to prevent the filter element, the sample tubing and the analyser from blocking and blinding. Prime features include:

- Self-cleaning sample filtration with various pore sizes
- Automatic cleaning action: blowback by solenoid controlled instrument air
- Static Pressure Regulator assures a constant, readily available sample level at atmospheric pressure
- PLC or analyser controlled cleaning frequency

Specificații

| | |
|--------------------------|----------------------------------------------------------|
| Caracteristici speciale: | Immersion Version |
| Clasa de protecție: | IP55 |
| Cleaning: | Automatic blowback by solenoid controlled instrument air |
| Dimensiune por: | 50 µm |
| | Optional: |
| | 100 µm, 200 µm |

| | |
|--------------------------------------------|-----------------------------------------------------------------------------------------|
| Dimensiuni (Înălțime x Lățime x Adâncime): | 750 mm x 550 mm x 200 mm |
| Earth connection: | Dry and clean earth pole with low impedance (< 1 Ohm) using an earth cable of > 2.5 mm² |
| Greutate: | 12 kg |
| Instrument air: | Dry and oil free according to ISA-S7.0.01-1996 quality standard for instrument air |
| Material: | Filter: SS 316L |
| | Piping: PVC |
| | Manual ball valves: PVC |
| | Tubing: Norprene, PFA, PE |
| | Static Pressure Regulator: PMMA |
| | Panel: weather resistant Trespa |
| Note speciale: | Backflush valve controlled by Analyzer |
| Nr. flux probe : | 1 stream |
| Putere: | 24 VDC, powered by analyser or external supply |
| Required fast loop: | 2 m/s |
| Scurgere: | Sample return line 1" BSF; overflow Static Pressure Regulator 3/8" OD |
| Size: | 50 µm |
| Temperatura probă: | Max. 65 °C |
| Tuburi: | Up to 3 m |
| | Optional: |
| | up to 3 m with heating |
| | up to 6 m |
| | up to 6 m with heating |
| | up to 10 m |
| | up to 10 m with heating |
| | up to 15 m |
| | up to 15 m with heating |
| | up to 20 m |
| | up to 20 m with heating |